

**36021 & 36026V7Z MILTOUCH (HIGH VOLTAGE)
300G with Accelerometer
V1000 INVERTER**

CONSTANT	VALUE	CONSTANT	VALUE
A1-01	2 Note 3	E1-10	16
A1-02	0	E2-01	Note 1
A1-03	Note 2	H1-03	7
B1-01	1	H1-04	4
B1-02	1	H1-05	3
B1-03	0	H1-06	5
B1-17	1	H1-07	A
C1-01	35	H2-01	E
C1-02	20	H3-03	100 Note 4
C1-03	120	H3-04	0 Note 4
C1-04	80	L1-01	0
C2-01	1.0	L2- 01	2
C4-01	.7	L3-01	0
C6-01	1	L3-04	0
C6-02	2	L3-05	0
E1-01	460	L8-05	0
E1-03	F	L8-07	0
E1-04	200	H1-01	40
E1-05	460	H1-02	41
E1-06	60	H2-02	16
E1-07	3	L4-03	167
E1-08	23	L4-04	10
E1-09	1.5		

- Note 1: Enter Ampere rating of inverter
 Note 2: 2220 is initialize - otherwise 0
 Note 3: Set to 0 after programming
 Note 4: Modify to set speeds when D/A is used

Accelerometer setting: 10 lb weight min speed 160 max speed 185 3626
 8 lb weight min speed 160 max speed 185 3621

Release Date: July 21, 2014

Revision C